Technical Data Sheet AQUA Glaslack Print P01-BD

Rhenocoll
THE GLOBAL COATINGS + ADHESIVES COMPANY

Version: 2009/06 , page 1 of 2

AQUA - Glaslack Print P01-BD, for screen printing (VP 5760)

Eco-friendly, water-based varnish

Colors: P01-BD opaque colors, various color charts (e.g. RAL)

Degree of gloss: silk-mat

Features: Ready-to-use 1-component water-based varnish for glass surfaces with screen printing. Can be used as a screen or for decorative designs. Abrasion and scratch resistant (according DIN 68861-4A > 4 N). Excellent adhesion according to DIN EN ISO 2409 (GT = 0), resistant against water and common cleaning agents. No yellowing. AQUA Glaslack is to be applied in one layer, several prints are possible. Follow-up coats are possible with Glaslack G1, G2 or G12.

Art. No.: A 4569

Addition of promoter: Only necessary if the first varnish layer is used directly on the glass. Not necessary in further steps.

Add 2% TEC – Bond-Promotor 01 to the varnish (1 Liter varnish + 20 ml Promotor). Stir in by hand.

Application: Screen printing

Addition of Promoter: Only necessary if applied as a first coat directly onto glass. Not necessary for follow-up coats. Add at a ratio of 2% promoter to the varnish (1 liter varnish + 20 ml promoter). Mix manually.

Processing time (pot life) after the promoter was added: Within one working day (8-12 hrs). After this time, the mixture can be used in the following steps, but not directly onto glass anymore. A change in viscosity is possible after a few days.

Dilution: With water

Cleaning: With water, immediately after use. Dried varnish can be removed with universal thinner or acetone.

Drying: At 20°C and 65% relative humidity: dust dry after 30 min., touch dry after 50 min. For complete drying leave over night.

Subsurface: Glass

Pre-treatment: Glass surface must be cleaned prior to varnishing

Finishing treatment: Aqua Glaslack (if needed)

Consumption: Depending on the type of print screening

VOC 2010: Cat. I / Base Wb / max value 140 g/L / IST value 0 g/L.

Technical Data Sheet AQUA Glaslack Print P01-BD

P01-BD Art. No.: A 4569



Version: 2009/06 , page 2 of 2

Storage: Store up to 12 months in the original container. Do not store or transport below +7°C and not above +30°C, close firmly.

Supply units:

1 liter can

5 liter pail

20 liter pail

Disposal: Not fully hardened or completely dried out left over product are to be disposed of as special waste (AVV waste code no. 030202). Recycle empty containers.

Ecology: Left over varnish not to be disposed of into waters. The product is hazardous to water according to the German Water Act §19. WGK = 1 (self-classification).

Labeling:

VbF: n/a

GefStoffV: no labeling required GGVS: no labeling required

Safety information: Keep locked up and out of reach of children. Avoid contact with eyes. In case of contact with eyes, wash immediately with plenty of water.

Service:

Our service team for application technology is available to you at any time without obligation.

Phone: ++49 (0)6384 99 38 - 0 Fax: ++49 (0)6384 99 38 - 112

Email: info@rhenocoll.de

The information given within is without obligation and is based on practical experience as well as on experiments which we have carried out and are not attribute guaranties in the sense of the newest BGH legal requirements. We recommend that in any case users carry out their own tests since we have no influence over the large diversity of materials and their processing. No liability for the manufacturer can be derived from the contents of this data sheet. Statements going beyond or deviating from the contents of this data sheet require the written confirmation of the company headquarters. Our General Terms & Conditions apply in any case.

With the release of this Technical Data Sheet all previous versions become obsolete.